

Switch Hero 8

Your safety is our priority

8-Hour Hero

Application

Our GPO is easily installed by a registered electrician and once it is turned on and customised, it will only operate for up to 8 hours.

Prevent the risk to your environment of battery operated wheelchairs and scooters.

The 8-Hour Hero keeps a battery operating equipment safe from overheating and possibly exploding.

Features

- **FIRE** retardent double GPO made with VO material.
- Tempered glass panel easily cleaned and never fades.
- Capacitive easy touch power on button.
- MCU Intelligent Smart Chipset, 3 Year Warranty.
- Automatic cut-off of power 2 hours (can be customised).
- Complies with Australian Standards and Approvals.



SAFETY FIRST



Specifications

- Colours available with and black.
- Size 120 x 72 x 42mm.
- Capacitive easy touch power on button.
- Operating Voltage: 110-240V AC/50Hz-60Hz.
- Rated Current: 10A x 2
- Material: toughened glass panel + fire retardant shell

Contact us

www.acsesshealth.com.au

info@acsess.com.au

1300 736 785